

Analyzer

Waveform MACHINE 1

Acq. Control

Print

Run

Accumulate
On

A_CLK

X -> 1

Hex

0 -> 1

Center
Screen

sec/Div
50.0 us

Delay

223.0 us

Markers
Time

X to 0
440.0 ns

Trig to X
1.020 ms

Trig to 0
1.021 ms

A_CLK

A_CS

A_OUT

A_IN

TEST

RVS

