

Point Format	Y
Horizontal Units	s
Horizontal Scale	0.0004
Horizontal Delay	0.100134
Sample Interval	4.00E-07
Record Length	10000
Gating	0.0% to 100.0%
Probe Attenuation	10
Vertical Units	V
Vertical Offset	0
Vertical Scale	1
Vertical Position	-3.94




Fig. 1 A signal 10010000A00000001A10000101A10000000A




Fig. 2 B signal 10010001A10000101A10000000N




Fig. 3 C signal 10010000A00000000A10000101A10000000A




Fig. 4 D signal 10010001A00000000A00000000N