


Lab Notebook Entry from LeCroy DSO
DSO S/N: LCRY2801N55750
User: LeCroyUser
Time: 3/11/2019 4:01:41 PM

3/11/2019 4:01:41 PM



Battery removed early



Channel Status

	C1	C2	C3	C4
Vertical	V / Div	2.00 V	1.00 V	1.00 V
	Offset	-6.050 V	-1.060 V	-1.075 V
	Coupling	DC1MΩ	DC1MΩ	DC1MΩ
	BW-Limit	1GHZ	1GHZ	1GHZ
	Probe	10	10	10
	Sweeps	1 #	1 #	1 #

Acquisition Status

Horizontal	Time / Div	500 μs	Sampling Rate	500.000000 MS/s
	Time / Pt	2.000000 ns	Sampling Mode	RealTime
	Pts / Div	250.0000 kS	Trigger Delay	-790 μs
	Mode	Stop	Slope	Negative
Trigger	Type	Edge	Level	1.27 V
	Source	C4	Coupling	DC