

- Ver 1-3, R78 NM R69 0ohm
Ver 4, R78 10k R69 470ohm
Ver 5, R78 10k R69 1k
Ver 6, R78 10k R69 1k5
Ver 7, R78 10k R69 2k2
Ver 8, R78 10k R69 2k7
Ver 9, R78 10k R69 3k3
Ver 10, R78 10k R69 3k9
Ver 10, R78 10k R69 4k7
Ver 11, R78 10k R69 5k6
Ver 12, R78 10k R69 6k8
Ver 13, R78 10k R69 8k2
Ver 14, R78 10k R69 10k