







CH1: CLKOUT
 CH2: nRESET
 CH3: DVDD
 CH4: CVDD

Ch1	5.00 V	Ch2	5.00 V	M	200ns	A	Ch2	1.40 V
Ch3	5.00 V	Ch4	2.00 V					

10.20 %