



Results (Measure All Edges)

Measurement	Current	Min	Max
ΔTime(3-3)	1.62846 ns	974.79 ps	2.50785 ns

Markers

X1	-1.67254 ns
X2	-44.07 ps
ΔX	1.62846 ns
1/ΔX	614.076 MHz
Y1	0.0 V
Y2	0.0 V
ΔY	0.0 V
ΔY/ΔX	0.0 V/s