



bootp

No.	Time	Source	Destination	Protocol	Length	Info
2	0.001780	0.0.0.0	255.255.255.255	DHCP	342	DHCP Discover - Transaction ID 0x88fa9967
10	1.059426	0.0.0.0	255.255.255.255	DHCP	342	DHCP Discover - Transaction ID 0x88fa9967
17	3.663506	0.0.0.0	255.255.255.255	DHCP	342	DHCP Discover - Transaction ID 0x88fa9967
22	8.419613	0.0.0.0	255.255.255.255	DHCP	342	DHCP Discover - Transaction ID 0x88fa9967
25	16.680000	0.0.0.0	255.255.255.255	DHCP	342	DHCP Discover - Transaction ID 0x88fa9967
64	24.898301	0.0.0.0	255.255.255.255	DHCP	342	DHCP Discover - Transaction ID 0x88fa9967
71	33.324923	0.0.0.0	255.255.255.255	DHCP	342	DHCP Discover - Transaction ID 0x88fa9967

- > Frame 2: 342 bytes on wire (2736 bits), 342 bytes captured (2736 bits) on interface en2, id 0
- > Ethernet II, Src: Apple_f3:57:e6 (ac:29:3a:f3:57:e6), Dst: Broadcast (ff:ff:ff:ff:ff:ff)
- > Internet Protocol Version 4, Src: 0.0.0.0, Dst: 255.255.255.255
- > User Datagram Protocol, Src Port: 68, Dst Port: 67
- > Dynamic Host Configuration Protocol (Discover)

0000	ff ff ff ff ff ff ac 29 3a f3 57 e6 08 00 45 00) :W...E.
0010	01 48 ad f4 00 00 ff 11 0c b1 00 00 00 00 ff ff	.H.....
0020	ff ff 00 44 00 43 01 34 ac d0 01 01 06 00 88 fa	...D.C.4
0030	99 67 00 00 00 00 00 00 00 00 00 00 00 00 00	.g.....
0040	00 00 00 00 00 00 ac 29 3a f3 57 e6 00 00 00 00) :W.....
0050	00 00 00 00 00 00 00 00 00 00 00 00 00 00 00
0060	00 00 00 00 00 00 00 00 00 00 00 00 00 00 00
0070	00 00 00 00 00 00 00 00 00 00 00 00 00 00 00
0080	00 00 00 00 00 00 00 00 00 00 00 00 00 00 00
0090	00 00 00 00 00 00 00 00 00 00 00 00 00 00 00
00a0	00 00 00 00 00 00 00 00 00 00 00 00 00 00 00
00b0	00 00 00 00 00 00 00 00 00 00 00 00 00 00 00
00c0	00 00 00 00 00 00 00 00 00 00 00 00 00 00 00
00d0	00 00 00 00 00 00 00 00 00 00 00 00 00 00 00
00e0	00 00 00 00 00 00 00 00 00 00 00 00 00 00 00
00f0	00 00 00 00 00 00 00 00 00 00 00 00 00 00 00
0100	00 00 00 00 00 00 00 00 00 00 00 00 00 00 00
0110	00 00 00 00 00 00 63 82 53 63 35 01 01 37 0c 01c Sc5..7..
0120	79 03 06 0f 6c 72 77 fc 5f 2c 2e 39 02 05 dc 3d	y...lrw _,.9...=
0130	07 01 ac 29 3a f3 57 e6 33 04 00 76 a7 00 ff 00	...) :W 3..v....
0140	00 00 00 00 00 00 00 00 00 00 00 00 00 00 00
0150	00 00 00 00 00 00