

Comment	Description	Designator	Footprint	LibRef	Quantity
CAP_SMD0805	CAP_SMD0805	C1, C2, C3, C4, C5, C6, C7, C8, C11, C14, C15, C21, C22, C23, C25, C26, C27, C28, C29, C31, C32, C33, C34, C35, C36, C37, C38, C39, C40, C41, C42, C43, C44, C45, C46, C47, C48, C49, C50, C51, C52, C53, C54, C71, C72, C73, C74, C75, C76, C77, C78, C79, C80, C81, C82, C83, C84, C85, C86, C91, C92, C93, C94	CAP_SMD0805	CAP_SMD0805, CAP_SMD0805_VARIANT_1	63
CAP_SMD8X8	CAP_SMD8X8	C12, C24	CAP_SMD8X8	CAP_SMD8X8	2
CAPBP_SMDC	CAPBP_SMDC	C13	CAPBP_SMDC	CAPBP_SMDC	1
LED_3MMRH	LED_3MMRH	D1	LED_3MMRH	LED_3MMRH	1
SS14	SS14	D11	SS14	SS14	1
LL4148	LL4148	D12	LL4148	LL4148	1
SS16	SS16	D21	SS16	SS16	1
1N5312	1N5312	D31, D32	1N5312	1N5312	2
HEADER_4X1	HEADER_4X1	J1	HEADER_4X1	HEADER_4X1	1
CJ48-1P	CJ48-1P	J2	CJ48-1P	CJ48-1P	1
SBDK174	SBDK174	J31, J32	SBDK174	SBDK174	2
FERRITE_SMD0805	FERRITE_SMD0805	L1, L2, L22, L23, L31, L32, L71, L72, L91	FERRITE_SMD0805	FERRITE_SMD0805	9
MSS1048	MSS1048	L21	MSS1048	MSS1048	1
L78L05ABD	L78L05ABD	P11	L78L05ABD	L78L05ABD	1
LMR64010	LMR64010	P21	LMR64010	LMR64010	1
SPX1117R-3-3	SPX1117R-3-3	P22	SPX1117R-3-3	SPX1117R-3-3	1
RES_SMD0805	RES_SMD0805	R1, R2, R3, R4, R5, R21, R22, R23, R24, R31, R32, R33, R34, R35, R36, R37, R38, R39, R40, R41, R42, R43, R44, R45, R46, R47, R48, R49, R50, R51, R52, R53, R54, R55, R56, R57, R58, R59, R60, R61, R62, R71, R72, R73, R74, R75, R76, R77, R78, R79, R80, R81, R82, R91, R92, R93, R94, R95	RES_SMD0805	RES_SMD0805, RES_SMD0805_VARIANT_1, RES_SMD0805_VARIANT_2	58
R5F211B	R5F211B	U1	R5F211B	R5F211B	1
ADR391A	ADR391A	U21	ADR391A	ADR391A	1
PGA280	PGA280	U31, U32	PGA280	PGA280	2
ADS1292	ADS1292	U71	ADS1292	ADS1292	1
TXS0102DCT	TXS0102DCT	U72	TXS0102DCT	TXS0102DCT	1
SP485EN	SP485EN	U91	SP485EN	SP485EN	1