

Application PTQA420050N2AD x2 +5V5Vout with N+1 Diode Oring

Review Diode VF(Instantaneous Voltage) Suggest MBRB2515(25Amps)= 0.23 V VF from 0.1A to 10A

Adjust resistor may require new value for lower Vout

