

- Integration up mode
- range 7
- integration time 14 μ s

A (V)	resistor Ohm	current (nA)	out_pos (V)	out_neg (V)
1.69	8.20E+06	0	2.3	0.85
1.5	8.20E+06	23.171	2.25	0.91
1.2	8.20E+06	59.756	2.13	1.02
0.8	8.20E+06	108.537	1.99	1.18
0.5	8.20E+06	145.122	1.88	1.54
0.2	8.20E+06	181.707	1.78	1.66
0	8.20E+06	206.098	1.72	1.67
-0.2	8.20E+06	230.488	1.76	1.69
-0.4	8.20E+06	254.878	1.94	1.7
-0.8	8.20E+06	303.659	2.27	1.72

