

Bandpass filter CC430EM Rev 3

L413=L415=15nH Murata LQW15A 2% tolerance

C412=C414=1.5pF Murata GRM15 serie

L414=2.2nH Murata LQP15M serie +/-0.1pF tolerance

C413=8.2pF Murata GRM15 serie (+/- 0.1pF preferable or +/- 0.25pF max tolerance if high tolerance is not available)

