



C28, C30, C37 and C38: It is important to choose either a 120nF or 1210 component for these decoupling capacitors to have the possibility to take the audio output directly under the capacitor in layout!



OUTPUT INDUCTOR STUFFING OPTION:



3 OHM LOAD OPERATION:

