

+ 18489	15:51:39.2318255	0.0897389	UsbSpec	Bulk In Transfer
+ 18491	15:51:39.3217576	0.1997725	UsbSpec	Bulk In Transfer
+ 18493	15:51:39.5255391	0.1959730	UsbSpec	Bulk In Transfer
- 18495	15:51:39.7217568	0.1047138	UsbSpec	Bulk In Transfer - USBD_STATUS_BUFFER_OVERRUN
- 18495	15:51:39.7217568		Microsoft_Windows_U_	Dispatch URB_FUNCTION_BULK_OR_INTERRUPT_TRANSFER
18...	15:51:39.7217568		Etw	{c88a4ef5-d048-4013-9408-e04b7db2814a}, EventID: 26, ProcessID: 4320, ThreadID: 3140, Size: 239
- 18496	15:51:39.8264706		Microsoft_Windows_U_	Complete URB_FUNCTION_BULK_OR_INTERRUPT_TRANSFER
18...	15:51:39.8264706		Etw	{c88a4ef5-d048-4013-9408-e04b7db2814a}, EventID: 70, ProcessID: 4124, ThreadID: 1088, Size: 239
+ 18497	15:51:39.8265853	0.4557985	UsbSpec	Bulk In Transfer - Canceled
+ 18508	15:51:40.2799581		Microsoft_Windows_USB_	Dispatch URB_FUNCTION_ABORT_PIPE
+ 18510	15:51:40.2824282		Microsoft_Windows_USB_	Complete URB_FUNCTION_ABORT_PIPE
+ 18511	15:51:40.2839364	0.4523587	UsbSpec	Bulk In Transfer - Canceled
+ 18513	15:51:40.7334284		Microsoft_Windows_USB_	Dispatch URB_FUNCTION_ABORT_PIPE
+ 18515	15:51:40.7363347		Microsoft_Windows_USB_	Complete URB_FUNCTION_ABORT_PIPE
+ 18521	15:51:40.7364180	0.4528018	UsbSpec	Bulk In Transfer - Canceled

Message Stack 1

2 Origins

18495 : UsbSpec	18496 : M
Bulk In Transfer - USBD_ST	Dispatch UR
18495 : E	18496 : E
{c88a4ef5-dl	{c88a4ef5-dl

Details 1

Enter search text here...

Name	Value	Bit Offset	Bit Length	Type
Status	USB_D_STATUS_BUFFER_OVERRUN(3221225484) (0xc000000c)			UsbdStatus
NtStatus	STATUS_SUCCESS(0) (0x00000000)			NTSTATUS
LengthRequested	192 (0x000000c0)			UInt32
LengthCompleted	0 (0x00000000)			UInt32
Direction	In(1) (0x00000001)			UsbDirection
Type	Bulk(2) (0x00000002)			UsbTransferType
EndpointAddress	0x81 (0x81)			Byte
DeviceInstance	2 (0x00000002)			Int32
UrbPtr	2231324024 (0x000000084FF4D78)			UInt64
TransferData				BinaryValue

Field Data

--