



Conditions


VIN: 34V
IO : 0mA
VO : 3.3V




VIN: 34V
IO : 150mA




VIN: 34V
IO : 336mA
(worst condition)





VIN: 34V
IO : 350mA



VIN: 34V
IO : 500mA