



Par: 26.1 V VBP W/ Vdd = 4.5v *



Temperature Analysis (Black - q1, q2, q3) (Red - Avg)



Sig	Shift	Avg	q2	Std	Cpk-	Cpk+
	Assembly					
	Burn-In					
	temperature	-0.062	-0.062	-0.001	3.1	9.5
	temperature =	150	150	85	0	125

Ref	Grp	level	temperature	Count		Prod Limits		Stats				Percentiles			Outliers (3s)		Capability		level Shift	
				Tested	Used	Lower	Upper	min	Avg	max	Stdev	q1	q2	q3	Low	Hi	Cpk-	Cpk+	Avg	Med
R	1	-55	-55	29	29	4.1999	4.6999	4.4064	4.4219	4.4289	0.0050	4.4176	4.4225	4.4253	0	0	14.6	18.2	-	-
	2	-40	-40	29	29	4.1999	4.6999	4.4070	4.4202	4.4272	0.0049	4.4168	4.4212	4.4232	0	0	14.9	18.9	-0.001	-0.001
	3	0	0	28	28	4.1999	4.6999	4.3998	4.4101	4.4163	0.0039	4.4075	4.4107	4.4120	0	0	17.6	24.3	-0.011	-0.011
	4	25	25	29	29	4.1999	4.6999	4.3899	4.4009	4.4085	0.0041	4.3975	4.4017	4.4025	0	0	16.0	23.8	-0.020	-0.020
	5	85	85	29	29	4.1999	4.6999	4.3706	4.3790	4.3856	0.0038	4.3766	4.3797	4.3814	0	0	15.4	27.6	-0.042	-0.042
	6	100	100	29	29	4.1999	4.6999	4.3645	4.3736	4.3797	0.0041	4.3712	4.3748	4.3761	0	0	14.0	26.4	-0.048	-0.047
	7	125	125	29	29	4.1999	4.6999	4.3576	4.3665	4.3737	0.0040	4.3636	4.3671	4.3691	0	0	13.8	27.7	-0.055	-0.055
	8	150	150	28	28	4.1999	4.6999	4.3505	4.3597	4.3671	0.0042	4.3562	4.3603	4.3621	0	0	12.6	26.9	-0.062	-0.062