



Par: 19.1 V VBP W/15mA load *



Temperature Analysis (Black - q1, q2, q3) (Red - Avg)



Sig	Shift	Avg	q2	Std	Cpk-	Cpk+
	Assembly					
	Burn-In					
	lot_id	5.4275	5.3708	-0.094	128.1	-2.2
	lot_id =	30	30	20	20	30

Ref	Grp	level	lot_id	Count		Spec Limits		Stats				Percentiles			Outliers (off)		Capability		level Shift	
				Tested	Used	Lower	Upper	min	Avg	max	Stdev	q1	q2	q3	Low	Hi	Cpk-	Cpk+	Avg	Med
R	1	4.5	4.5	10	10	0	9	2.3447	2.5820	2.7488	0.1136	2.4995	2.6270	2.6424	0	0	7.6	18.8	-	-
	2	10	10	10	10	0	9	7.8463	7.8692	7.9031	0.0205	7.8502	7.8586	7.8846	0	0	127.4	18.3	5.2871	5.2315
	3	15	15	10	10	0	9	7.9288	7.9527	7.9882	0.0198	7.9379	7.9411	7.9646	0	0	133.7	17.6	5.3707	5.3140
	4	20	20	10	10	0	9	7.9546	7.9773	8.0114	0.0195	7.9604	7.9653	7.9910	0	0	135.7	17.4	5.3953	5.3382
	5	25	25	10	10	0	9	7.9700	7.9948	8.0286	0.0197	7.9801	7.9839	8.0081	0	0	135.0	17.0	5.4127	5.3568
	6	30	30	10	10	0	9	7.9850	8.0095	8.0461	0.0198	7.9963	7.9979	8.0209	0	0	134.3	16.6	5.4275	5.3708