


DRV8432DKDEVM
6513484 RevA



BOARDS DIMS = 130x80mm

Through Holes			
Diameter (in)	Tolerance (in)	Quantity	Symbol
0.010	+/- 0.003	65	+
0.014		256	+
0.025		6	⊠
0.030		10	⊠
0.035		20	○
0.040		41	×
0.040		6	△
0.060		4	○
0.070		4	□
0.115		8	○

NOTES TO FAB

1. ALL PLATED THROUGH HOLES TO BE CHEMICALLY CLEANED
2. END ITEM TO MEET OR EXCEED IPC-A-600.
3. MATERIAL: FR4.
4. FINISHED THICKNESS = .002 +/- .005
5. ALL COPPER WEIGHT = 2 OZ.
6. POSITION ACCURACY = +/- .0015
7. APPLY BLUE ENTHONE SOLDERMASK TO BOTH SIDES OF BOARD. SEPARATE ARTWORK FOR TOP AND BOTTOM.
8. APPLY WHITE LPI SILKSCREEN TO TOP SIDE OF BOARD ONLY.
9. WARPAGE = +/- .005 PER LINEAR INCH MAX.
10. SWOBC.
11. EMULSION NICKEL GOLD. (ENIG)
12. ALL HOLES ARE PLATED UNLESS OTHERWISE STATED.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS IN INCHES

TOLERANCES: CORNERS = .075 R MAX
ANGLES +/- 5 DEGREES

HOLE DIAMETERS: <=.080 = +/- .003
>.080 = +/- .004

DIMENSIONAL LIMITS APPLY AFTER PLATING AND COATING