



Par: 20.1 V VBP Enabled *0mA load



Temperature Analysis (Black - q1, q2, q3) (Red - Avg)



Sig	Shift	Avg	q2	Std	Cpk-	Cpk+
	Assembly Burn-In					
	lot_id	3.8365	3.8302	0.0192	-642.0	-796.7
	lot_id =	30	30	10	10	10

Ref	Grp	level	lot_id	Count		Spec Limits		Stats				Percentiles			Outliers (off)		Capability		level Shift	
				Tested	Used	Lower	Upper	min	Avg	max	Stdev	q1	q2	q3	Low	Hi	Cpk-	Cpk+	Avg	Med
R	1	4.5	4.5	10	10	0	9	4.3887	4.3911	4.3937	0.0018	4.3894	4.3906	4.3934	0	0	771.2	809.4	-	-
	2	10	10	10	10	0	9	8.1635	8.1902	8.2250	0.0211	8.1702	8.1841	8.2047	0	0	129.2	12.8	3.7991	3.7934
	3	15	15	10	10	0	9	8.1902	8.2119	8.2468	0.0194	8.1944	8.2042	8.2273	0	0	140.9	13.5	3.8208	3.8136
	4	20	20	10	10	0	9	8.1978	8.2209	8.2546	0.0192	8.2044	8.2136	8.2364	0	0	142.5	13.5	3.8298	3.8229
	5	25	25	10	10	0	9	8.2033	8.2263	8.2593	0.0183	8.2094	8.2194	8.2397	0	0	149.7	14.1	3.8352	3.8288
	6	30	30	10	10	0	9	8.2066	8.2276	8.2616	0.0182	8.2101	8.2208	8.2390	0	0	150.7	14.1	3.8365	3.8302