

pbq®




Lithium Ferro Phosphate (LiFePO₄)

pbq 12-12 / 15-12 LiFe



Leading in quality




Voltage : 12.8 Volt
Appr. dimensions : 151x98x101 mm (LxWxH)
Terminal : Faston 250
Container & lid : Flame Retardant ABS

Operating temperature
Charge : -30°C ~ 60°C
Discharge : -30°C ~ 60°C
Storage : -30°C ~ 50°C

Specifications		pbq 12-12 LiFe	pbq 15-12 LiFe
Nominal	Capacity	12 Ah	15 Ah
Weight	(appr.)	1.6 Kg	1.9 Kg
Internal	Resistance	<45mΩ	<38mΩ
Specific	Energy	96 Wh/Kg	101 Wh/Kg
Standard Discharge at 25°C	Max. Cont. Current	20A	20A
	Max. 30 sec. pulse	30A	30A
	Cut off Voltage	8.0V	8.0V
Standard Charge	Charge Voltage	14.8V	14.8V
	Float	13.8V	13.8V
	Style	CC/CV	CC/CV
	Recommended Charge Time	6A 2.5h	7.5A 2.5h

Note: Do not use more than three batteries in series



The rechargeable pbq LiFe battery employs lithium iron phosphate as its cathode and carbon as its anode. The electrolyte salt dissolves in organic compound solvent and the electrolyte system is absorbed by the separators and the plates. All batteries of this type have a special one-way valve to allow the disaggregate-tire solvent gases to escape.

Each individual cell is spiral wound and formed to a prismatic cell. The nominal cell voltage is 3.2V. Four cells are placed in series in order to create 12.8V.

To protect the battery from over charging and over discharging the battery is equipped with a internal battery management system (BMS). The BMS also takes care of the balance between the internal cell.

To avoid overheating of the battery, a special insertion, called PTC, is added to the electrolyte. This additive neutralizes the electrolyte and disables the battery permanently if the internal temperature exceeds 80°C.

General features

- More than 2000 deep cycles, pbq LiFe offers the lowest life-cycle costs, using a graphite anode.
- The battery may be installed in any direction, upside down is not recommended
- Excellent high-rate discharge an recharge capabilities
- Third the weight of an equivalent lead acid battery
- Long service life in floating application
- Maintenance free operation
- Excellent safety
- Environmental friendly due to the absence of heavy metals

Contact your pbq dealer

or visit our website

www.pbq-batteries.com

63,5 mm x 33,8 mm (bv. HERMA 4227)