



Address: No.35, Aly.21, Ln 228, Ankang Rd, Neihu, Taipei
Tel: +886-2-6606-8877
Fax: +886-2-6606-8875

Radiated Emission Measurement

Operator: Roy

File : 2596K
72.0 dBuV/m


Data : #1

Date: 2014/10/20

Temperature: 24 °C

Time: 下午 03:16:23

Humidity: 60 %



Site : 966 Chamber

Condition : CISPR22 RE-Class B 10M

EUT : Booking (錄森)

M/N: 2596K

Test Mode : 48V(new)

Note : 1.2

Polarization: **Vertical**

Power : 230 V.a.c.

Distance: 10m

Mk.	Frequency (MHz)	Reading (dBuV)	Detector	Corr. factor (dB/m)	Result (dBuV/m)	Limit (dBuV/m)	Ant.Pos (cm)	Tab.Pos (deg.)	Margin (dB)	Comment
X	45.5511	30.58	peak	4.28	34.86	30.00			4.86	
*	64.7555	28.50	QP	9.43	37.93	30.00	100	231	7.93	
X	94.1483	27.91	peak	3.98	31.89	30.00			1.89	
X	105.8116	29.60	peak	5.42	35.02	30.00			5.02	
X	163.7375	25.32	QP	11.27	36.59	30.00	100	0	6.59	
	172.3407	19.15	QP	8.27	27.42	30.00	100	0	-2.58	

*:Maximum data x:Over limit !:over margin



Address: No. 35, Aly. 21, Ln 228, Ankang Rd, Neihu, Taipei
Tel: +886-2-6606-8877
Fax: +886-2-6606-8875

Radiated Emission Measurement

Operator: Roy

File : 2596K
72.0 dBuV/m


Data : #2

Date: 2014/10/20

Temperature: 24 °C

Time: 下午 03:45:43

Humidity: 60 %



Site : 966 Chamber

Condition : CISPR22 RE-Class B 10M

EUT : Booking (錄森)

M/N: 2596K

Test Mode : 48V(new)

Note : 1.2 c112-c115+10nf

Polarization: **Vertical**

Power : 230 V.a.c.

Distance: 10m

Mk.	Frequency (MHz)	Reading (dBuV)	Detector	Corr. factor (dB/m)	Result (dBuV/m)	Limit (dBuV/m)	Ant.Pos (cm)	Tab.Pos (deg.)	Margin (dB)	Comment
X	47.4950	30.33	peak	5.90	36.23	30.00			6.23	
X	66.2881	28.74	QP	8.62	37.36	30.00	100	284	7.36	
*	94.1483	34.13	peak	3.98	38.11	30.00			8.11	
X	164.1283	25.37	peak	11.29	36.66	30.00			6.66	
X	177.7355	30.32	peak	7.41	37.73	30.00			7.73	
X	199.1182	28.16	peak	5.97	34.13	30.00			4.13	
X	210.7816	26.90	peak	7.22	34.12	30.00			4.12	

*:Maximum data x:Over limit !:over margin



Address: No. 35, Aly. 21, Ln 228, Ankang Rd, Neihu, Taipei
Tel: +886-2-6606-8877
Fax: +886-2-6606-8875

Radiated Emission Measurement

Operator: Roy

File : 2596K
72.0 dBuV/m


Data : #3

Date: 2014/10/20

Temperature: 24 °C

Time: 下午 03:58:20

Humidity: 60 %



Site : 966 Chamber

Condition : CISPR22 RE-Class B 10M

EUT : Booking (錄森)

M/N: 2596K

Test Mode : 48V(new)

Note : v1.1

Polarization: **Vertical**

Power : 230 V.a.c.

Distance: 10m

Mk.	Frequency (MHz)	Reading (dBuV)	Detector	Corr. factor (dB/m)	Result (dBuV/m)	Limit (dBuV/m)	Ant.Pos (cm)	Tab.Pos (deg.)	Margin (dB)	Comment
X	47.4950	26.91	peak	5.90	32.81	30.00			2.81	
X	64.9900	27.04	peak	9.64	36.68	30.00			6.68	
*	94.3587	35.96	QP	4.05	40.01	30.00	100	104	10.01	
X	142.7455	27.59	peak	4.56	32.15	30.00			2.15	
X	173.8477	27.35	peak	8.35	35.70	30.00			5.70	
X	197.1743	26.00	peak	5.59	31.59	30.00			1.59	

*:Maximum data x:Over limit !:over margin



Address:No.35,Aly.21,Ln 228,Ankang Rd,Neihu,Taipei
Tel:+886-2-6606-8877
Fax:+886-2-6606-8875

Radiated Emission Measurement

Operator: Roy

File :2596K

Data :#4

Date: 2014/10/20

Temperature:24 °C

72.0 dBuV/m

Time: 下午 04:18:21

Humidity:60 %



Site : 966 Chamber

Condition : CISPR22 RE-Class B 10M

EUT : Booking (錄森)

M/N: 2596K

Test Mode : 48V(new)

Note : v1.1

Polarization: **Vertical**

Power : 230 V.a.c.

Distance: 10m

Mk.	Frequency (MHz)	Reading (dBuV)	Detector	Corr. factor (dB/m)	Result (dBuV/m)	Limit (dBuV/m)	Ant.Pos (cm)	Tab.Pos (deg.)	Margin (dB)	Comment
X	47.4950	28.73	peak	5.90	34.63	30.00			4.63	
X	64.9900	27.68	peak	9.64	37.32	30.00			7.32	
*	98.4670	37.09	QP	3.54	40.63	30.00	100	86	10.63	
X	105.8116	34.32	peak	5.42	39.74	30.00			9.74	
X	162.1844	27.81	peak	11.21	39.02	30.00			9.02	
X	173.8477	25.17	peak	8.35	33.52	30.00			3.52	

*:Maximum data x:Over limit !:over margin



Address: No. 35, Aly. 21, Ln 228, Ankang Rd, Neihu, Taipei
Tel: +886-2-6606-8877
Fax: +886-2-6606-8875

Radiated Emission Measurement

Operator: Roy

File : 2596K

Data : #5


Date: 2014/10/20

Temperature: 24 °C

72.0 dBuV/m

Time: 下午 04:37:43

Humidity: 60 %



Site : 966 Chamber

Condition : CISPR22 RE-Class B 10M

EUT : Booking (錄森)

M/N: 2596K

Test Mode : 48V(new)

Note : v1.2.1

Polarization: **Vertical**

Power : 230 V.a.c.

Distance: 10m

Mk.	Frequency (MHz)	Reading (dBuV)	Detector	Corr. factor (dB/m)	Result (dBuV/m)	Limit (dBuV/m)	Ant.Pos (cm)	Tab.Pos (deg.)	Margin (dB)	Comment
X	47.4950	27.65	peak	5.90	33.55	30.00			3.55	
X	64.9900	26.16	peak	9.64	35.80	30.00			5.80	
*	94.1483	39.11	peak	3.98	43.09	30.00			13.09	
X	105.8115	34.24	peak	5.42	39.66	30.00			9.66	
X	160.2405	27.84	peak	11.14	38.98	30.00			8.98	
X	193.2865	28.06	peak	4.79	32.85	30.00			2.85	
X	203.0060	27.78	peak	6.62	34.40	30.00			4.40	

*:Maximum data x:Over limit !:over margin



Address: No.35, Aly.21, Ln 228, Ankang Rd, Neihu, Taipei
Tel: +886-2-6606-8877
Fax: +886-2-6606-8875

Radiated Emission Measurement

Operator: Roy

File : 2596K
72.0 dBuV/m


Data : #6

Date: 2014/10/20

Temperature: 24 °C

Time: 下午 04:54:59

Humidity: 60 %



Site : 966 Chamber

Condition : CISPR22 RE-Class B 10M

EUT : Booking (錄森)

M/N: 2596K

Test Mode : 48V(new)

Note : v1.2.1 C149+10nF , R172+680k

Polarization: Vertical

Power : 230 V.a.c.

Distance: 10m

Mk.	Frequency (MHz)	Reading (dBuV)	Detector	Corr. factor (dB/m)	Result (dBuV/m)	Limit (dBuV/m)	Ant.Pos (cm)	Tab.Pos (deg.)	Margin (dB)	Comment
X	37.7756	26.69	peak	5.33	32.02	30.00			2.02	
X	47.4950	28.33	peak	5.90	34.23	30.00			4.23	
X	59.1583	28.93	peak	5.52	34.45	30.00			4.45	
X	84.4290	35.30	peak	0.66	35.96	30.00			5.96	
*	94.1483	39.36	peak	3.98	43.34	30.00			13.34	
X	105.8116	34.40	peak	5.42	39.82	30.00			9.82	
X	150.5210	25.34	peak	6.01	31.35	30.00			1.35	
X	164.1283	25.06	peak	11.29	36.35	30.00			6.35	
X	173.8477	25.08	peak	8.35	33.43	30.00			3.43	
	199.1182	23.80	peak	5.97	29.77	30.00			-0.23	

*:Maximum data x:Over limit !:over margin



Address: No. 35, Aly. 21, Ln 228, Ankang Rd, Neihu, Taipei
Tel: +886-2-6606-8877
Fax: +886-2-6606-8875

Radiated Emission Measurement

Operator: Roy

File : 2596K
72.0 dBuV/m


Data : #7

Date: 2014/10/20

Temperature: 24 °C

Time: 下午 05:06:17

Humidity: 60 %



Site : 966 Chamber

Condition : CISPR22 RE-Class B 10M

EUT : Booking (錄森)

M/N: 2596K

Test Mode : 48V(new)

Note : v1.2.1 C149+10nF , R172+680k , C221 Delete

Polarization: Vertical

Power : 230 V.a.c.

Distance: 10m

Mk.	Frequency (MHz)	Reading (dBuV)	Detector	Corr. factor (dB/m)	Result (dBuV/m)	Limit (dBuV/m)	Ant.Pos (cm)	Tab.Pos (deg.)	Margin (dB)	Comment
X	37.7756	26.22	peak	5.33	31.55	30.00			1.55	
X	47.4950	28.00	peak	5.90	33.90	30.00			3.90	
X	64.9900	27.83	peak	9.64	37.47	30.00			7.47	
*	94.1483	40.07	peak	3.98	44.05	30.00			14.05	
X	148.5772	29.47	peak	5.50	34.97	30.00			4.97	
X	162.1844	29.04	peak	11.21	40.25	30.00			10.25	
X	171.9038	29.42	peak	8.25	37.67	30.00			7.67	
X	201.0621	23.90	peak	6.31	30.21	30.00			0.21	

*:Maximum data x:Over limit !:over margin



Address: No.35, Aly.21, Ln 228, Ankang Rd, Neihu, Taipei
Tel: +886-2-6606-8877
Fax: +886-2-6606-8875

Radiated Emission Measurement

Operator: Roy

File : 2596K
72.0 dBuV/m

Data : #8

Date: 2014/10/20

Temperature: 24 °C

Time: 下午 05:22:27

Humidity: 60 %



Site : 966 Chamber

Condition : CISPR22 RE-Class B 10M

EUT : Booking (錄森)

M/N: 2596K

Test Mode : 48V(new)

Note : v1.2.1 C149+10nF , R172+680k , C221 Delete

Polarization: Vertical

Power : 230 Va.c.

Distance: 10m

Mk.	Frequency (MHz)	Reading (dBuV)	Detector	Corr. factor (dB/m)	Result (dBuV/m)	Limit (dBuV/m)	Ant.Pos (cm)	Tab.Pos (deg.)	Margin (dB)	Comment
X	45.5511	30.25	peak	4.28	34.53	30.00			4.53	
X	59.1583	29.10	peak	5.52	34.62	30.00			4.62	
*	97.7736	40.59	QP	3.69	44.28	30.00	100	312	14.28	
X	164.1283	25.97	peak	11.29	37.26	30.00			7.26	

*:Maximum data x:Over limit !:over margin



Address: No. 35, Aly. 21, Ln 228, Ankang Rd, Neihu, Taipei
Tel: +886-2-6606-8877
Fax: +886-2-6606-8875

Radiated Emission Measurement

Operator: Roy

File : 2596K
72.0 dBuV/m


Data : #9

Date: 2014/10/20

Temperature: 24 °C

Time: 下午 05:40:05

Humidity: 60 %



Site : 966 Chamber

Condition : CISPR22 RE-Class B 10M

EUT : Booking (錄森)

M/N: 2596K

Test Mode : 48V(new)

Note : v1.2.1 C149+10nF , R172+680k , C221 Delete

Polarization: **Vertical**

Power : 230 Va.c.

Distance: 10m

Mk.	Frequency (MHz)	Reading (dBuV)	Detector	Corr. factor (dB/m)	Result (dBuV/m)	Limit (dBuV/m)	Ant.Pos (cm)	Tab.Pos (deg.)	Margin (dB)	Comment
X	45.7415	25.72	QP	4.44	30.16	30.00	100	310	0.16	
X	60.2064	30.61	QP	5.41	36.02	30.00	100	310	6.02	
X	90.3387	28.21	QP	2.62	30.83	30.00	100	310	0.83	
X	106.6914	27.10	QP	5.76	32.86	30.00	100	70	2.86	
*	159.9860	26.65	QP	11.12	37.77	30.00	100	360	7.77	

*:Maximum data x:Over limit !:over margin



Address: No. 35, Aly. 21, Ln 228, Ankang Rd, Neihu, Taipei
Tel: +886-2-6606-8877
Fax: +886-2-6606-8875

Radiated Emission Measurement

Operator: Roy

File : 2596K
72.0 dBuV/m


Data : #10

Date: 2014/10/20

Temperature: 24 °C

Time: 下午 05:55:18

Humidity: 60 %



Site : 966 Chamber

Condition : CISPR22 RE-Class B (3M)

EUT : Booking (錄森)

M/N: 2596K

Test Mode : 48V(new)

Note : v1.2.1 C149+10nF , R172+680k , C221 Delete

Polarization: **Vertical**

Power : 230 V.a.c.

Distance: 3m

Mk.	Frequency (MHz)	Reading (dBuV)	Detector	Corr. factor (dB/m)	Result (dBuV/m)	Limit (dBuV/m)	Ant.Pos (cm)	Tab.Pos (deg.)	Margin (dB)	Comment
*	90.3547	35.31	QP	8.91	44.22	40.50	100	111	3.72	
X	105.8116	29.70	peak	11.79	41.49	40.50			0.99	

*:Maximum data x:Over limit !:over margin



Address: No. 35, Aly. 21, Ln 228, Ankang Rd, Neihu, Taipei
Tel: +886-2-6606-8877
Fax: +886-2-6606-8875

Radiated Emission Measurement

Operator: Roy

File : 2596K

Data : #11

Date: 2014/10/20

Temperature: 24 °C

72.0 dBuV/m

Time: 下午 06:40:24

Humidity: 60 %



Site : 966 Chamber

Condition : CISPR22 RE-Class B 10M

EUT : Booking (錄森)

M/N: 2596K

Test Mode : 48V(new)

Note : v1.2.1 C149+10nF , R172+680k , C221 Delete

Polarization: Vertical

Power : 230 V.a.c.

Distance: 10m

Mk.	Frequency (MHz)	Reading (dBuV)	Detector	Corr. factor (dB/m)	Result (dBuV/m)	Limit (dBuV/m)	Ant.Pos (cm)	Tab.Pos (deg.)	Margin (dB)	Comment
X	47.4950	27.77	peak	5.90	33.67	30.00			3.67	
X	59.1583	32.08	peak	5.52	37.60	30.00			7.60	
*	94.1483	35.96	peak	3.98	39.94	30.00			9.94	
X	159.1402	23.75	QP	10.68	34.43	30.00	100	359	4.43	

*:Maximum data x:Over limit !:over margin