

Trace width: 5mils, 0.000127m
Trace thickness: 1.4mils, 0.0000356m
Dielectric relative permittivity: 4.3
Trace capacitance/unit length (From online impedance calculator): 69.0538pF/m

SN74LVC574A
Octal Edge-Triggered D_FF
Continuous output current, IO: ±50 mA

SN74LVC541A
Octal Buffer/Driver
Continuous output current, IO: ±50 mA

SN74LVC541A
8-BIT DUAL-SUPPLY BUS TRANSCEIVER
Continuous output current, IO: ±50 mA

