




TPA2015D1YZHEVM

RevB



BOARD DIMS = 63mm x 59mm

Through Holes				
Diameter (mm)	Tolerance (mm)	Quantity	Plated	Symbol
0.15		4	Yes	◆
0.25		2	Yes	⊙
0.30	+0.10 / -0.00	77	Yes	⊠
0.61		20	Yes	⊠
0.89		2	Yes	⊙
3.25	+0.10 / -0.00	4	Yes	×
6.86		4	Yes	△
1.00x3.5mm SLOT		2	Yes	○
1.30x2.50mm SLOT		1	Yes	□
2.00mm SQUARE PUNCH TH		2	No	○

NOTES TO FAB

1. ALL PLATED THROUGH HOLES TO BE CHEMICALLY CLEANED BEFORE PLATING.
2. END ITEM TO MEET OR EXCEED IPC-A-600.
3. MATERIAL: FR-370HR.
4. FINISHED THICKNESS = 1.6mm +/- 0.125mm.
5. ALL COPPER WEIGHT = 1 OZ.
6. POSITION ACCURACY = +/- 0.0375mm.
7. APPLY BLUE ENTHONE SOLDERMASK TO BOTH SIDES OF BOARD.
SEPARATE ARTWORK FOR TOP AND BOTTOM.
8. APPLY WHITE LPI SILKSCREEN TO TOP SIDE OF BOARD ONLY..
9. WARPAGE = +/- 0.125mm PER 25mm INCH MAX.
10. SMOBC.
11. IMMERSION GOLD
12. ALL HOLES ARE PLATED UNLESS OTHERWISE STATED.

**UNLESS OTHERWISE SPECIFIED
DIMENSIONS IN MILLIMETERS**

TOLERANCES:

CORNERS = 1.75mm R MAX

ANGLES +/-5 DEGREES

HOLE DIAMETERS:

<=2.0mm = +/- 0.075mm

>2.0mm = +/- 0.01mm

**DIMENSIONAL LIMITS APPLY
AFTER PLATING AND COATING**