





C1	DC1M	C2	DC1M	C3	DC1M	C4	DC1M
2.00 V/div	5.00 V/div	5.00 V/div	1.00 V/div	5.00 V/div	5.00 V/div	1.00 V/div	1.00 V/div
-3.260 V ofst	4.70 V offset	4.70 V offset	-3.770 V ofst	10.05 V ofst	10.05 V ofst	-3.770 V ofst	-3.770 V ofst
1.298 V	-90 mV	-90 mV	45 mV	30 mV	30 mV	45 mV	45 mV
1.298 V	-90 mV	-90 mV	45 mV	30 mV	30 mV	45 mV	45 mV
Δy 0 mV	Δy 0.00 V	Δy 0.00 V	Δy 0.00 V	Δy 0.00 V	Δy 0.00 V	Δy 0.00 V	Δy 0.00 V


Timebase	-97 μ s	Trigger	C2 DC
50.0 μ s/div	50.0 μ s/div	Stop	3.15 V
10.0 kS	20 MS/s	Edge	Positive
X1= -153.00 μ s	ΔX = 0.00 μ s		
X2= -153.00 μ s	1/ ΔX = ---		



C1	DC1M	C2	DC1M	C3	DC1M	C4	DC1M
2.00 V/div	5.00 V/div	5.00 V/div	2.00 V/div	5.00 V/div	5.00 V/div	2.00 V/div	2.00 V/div
-3.260 V ofst	4.70 V offset	4.70 V offset	-7.540 V ofst	10.85 V ofst	10.85 V ofst	-7.540 V ofst	-7.540 V ofst
↓ 2.897 V	↓ -330 mV	↓ -330 mV	↓ -340 mV	↓ -340 mV	↓ -340 mV	↓ 1.483 V	↓ 1.483 V
↑ 3.472 V	↑ 210 mV	↑ 210 mV	↑ 80 mV	↑ 80 mV	↑ 80 mV	↑ 562 mV	↑ 562 mV
Δy 576 mV	Δy 540 mV	Δy 540 mV	Δy 420 mV	Δy 420 mV	Δy 420 mV	Δy -922 mV	Δy -922 mV


Timebase	-1.94 μs	Trigger	C4 DC
	1.00 μs/div	Stop	980 mV
10.0 kS	1.0 GS/s	Edge	Positive
X1=	4 ns	ΔX=	488 ns
X2=	492 ns	1/ΔX=	2.049 MHz

DRDY after SYNC pulse (Zoom Out)



C1	DC1M	C2	DC1M	C3	DC1M	C4	DC1M
2.00 V/div	5.00 V/div	5.00 V/div	2.00 V/div	5.00 V/div	5.00 V/div	2.00 V/div	5.00 V/div
-3.260 V ofst	4.70 V ofst	4.70 V ofst	-7.500 V ofst	10.85 V ofst	10.85 V ofst	-7.500 V ofst	10.85 V ofst
↓ 1.184 V	↓ 1.45 V	↓ 1.45 V	↓ 1.31 V	↓ 1.31 V	↓ 1.31 V	↓ 1.31 V	↓ 1.31 V
↑ 2.031 V	↑ 3.37 V	↑ 3.37 V	↑ 3.23 V	↑ 3.23 V	↑ 3.23 V	↑ 3.23 V	↑ 3.23 V
Δy 847 mV	Δy 1.92 V	Δy 1.92 V	Δy 1.92 V	Δy 1.92 V	Δy 1.92 V	Δy 1.92 V	Δy 1.92 V

Timebase	-388 μs	Trigger	C2 DC
	200 μs/div	Stop	3.15 V
10.0 kS	5.0 MS/s	Edge	Positive
X1=	0.0 μs	ΔX=	400 ns
X2=	400 ns	1/ΔX=	2.5 MHz



C1	DC1M	C2	DC1M	C3	DC1M	C4	DC1M
2.00 V/div	5.00 V/div	5.00 V/div	2.00 V/div	10.85 V/div	10.85 V/div	2.00 V/div	2.00 V/div
-3.260 V ofst	4.70 V ofst	4.70 V ofst	-7.500 V ofst	10.85 V ofst	10.85 V ofst	-7.500 V ofst	-7.500 V ofst
↓ 3.132 V	↓ 3.95 V	↓ 3.95 V	↓ 3.38 V	↓ 3.38 V	↓ 3.38 V	↓ 80 mV	↓ 80 mV
↑ 3.199 V	↑ 3.46 V	↑ 3.46 V	↑ 2.92 V	↑ 2.92 V	↑ 2.92 V	↑ 198 mV	↑ 198 mV
Δy 67 mV	Δy -490 mV	Δy -490 mV	Δy -460 mV	Δy -460 mV	Δy -460 mV	Δy 118 mV	Δy 118 mV

Timebase	-1.94 μs	Trigger	C2 DC
	1.00 μs/div	Stop	3.15 V
10.0 kS	1.0 GS/s	Edge	Positive
X1=	4 ns	ΔX=	488 ns
X2=	492 ns	1/ΔX=	2.049 MHz