



VCXO HCMOS


SMD-version

+3.3V


Voltage Controlled Crystal Oscillator

part no.	12.xxxxx	
model	KXO-72R	
frequency	27,0 MHz	
frequency stability	incl. all parameters	±50 ppm over -40°C ~ +85°C (referred to +25°C)
output	load	15 pF
	waveform	HCMOS
operating temperature range	-40°C ~ +85°C	
storage temperature range	-55°C ~ +125°C	
supply voltage range	+2.5 ~ +3.6V	
input voltage V _{DD}	+3.3V DC ±5%	
input current max.	15 mA (no load)	
start-up time max.	10 ms	
symmetry	45% / 55% at ½ V _{DD} level	
rise and fall time max.	5 ns	
frequency control voltage	1.65V ±1.35V	
frequency adjustment (pullability) min.	± 80 ppm	
phase jitter max.	1.0 ps	
phase noise max.	-80 dBc/Hz at 10 Hz -110 dBc/Hz at 100 Hz -135 dBc/Hz at 1 kHz -140 dBc/Hz at 10 kHz -145 dBc/Hz at 100 kHz -150 dBc/Hz at 1 MHz	
contents of reel	1000 pcs.	


Dimensions (mm):




Suggested soldering pad:




Reflow soldering condition:



Test circuit:



Tape specification:



Pin	Connection
1	VC
2	Tri-State
3	GND
4	OUTPUT
5	NC
6	V _{DD}