





REVISIONS			
REV	DESCRIPTION	DATE	APPROVED



Title *			
Size B	Document Number *	Rev *	
Date 4/13/2018	Drawn by *		
Filename 0166-MotorDrive REV0 CPU.SchDoc	Sheet *	of *	


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED

MOTOR 10

- Address
- 0001 = M1
 - 0010 = M2
 - 0011 = M3
 - 0100 = M4
 - 0101 = M5
 - 0110 = M6
 - 0111 = M7
 - 1000 = M8
 - 1010 = M10



Encoder Input
CHA=RB0
CHB=RB1
INDEX=RB2
HOME=RB3

BDC Motor

Motor Current Monitor

Title *			
Size B	Document Number *		Rev *
Date 4/13/2018	Drawn by *		
Filename 0166-MotorDrive REV0 M10.SchDoc		Sheet *	of *

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED

MOTOR 3

Address

0001 = M1

0010 = M2

0011 = M3

0100 = M4

0101 = M5

0110 = M6

0111 = M7

1000 = M8

1010 = M10

Encoder Input

CHA=RB0

CHB=RB1

INDEX=RB2


HOME=RB3

BDC Motor

Motor Current Monitor

Title *			
Size B	Document Number *		Rev *
Date 4/13/2018	Drawn by *		
Filename 0166-MotorDrive_REV0_M3.SchDdSheet * of *			

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED




Title *			
Size B	Document Number *	Rev *	
Date 4/13/2018	Drawn by *		
Filename 0166-MotorDrive_REV0_M5.SchDd	Sheet *	of *	

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED


MOTOR 8

- Address
- 0001 = M1
 - 0010 = M2
 - 0011 = M3
 - 0100 = M4
 - 0101 = M5
 - 0110 = M6
 - 0111 = M7
 - 1000 = M8
 - 1010 = M10



Title *			
Size	B	Document Number *	Rev *
Date	4/13/2018	Drawn by *	
Filename 0166-MotorDrive_REV0_M8.SchDdSheet * of *			


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED



Title *			
Size	B	Document Number *	Rev *
Date	4/13/2018	Drawn by *	
Filename 0166-MotorDrive_REV0_MAX3232CPE.DOC of *			

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED

8.5V - 17V Input Range
3.3V @ 1A



Title *			
Size B	Document Number *		Rev *
Date 4/13/2018	Drawn by *		
Filename 0166-MotorDrive_REV0_POWER.SchDoc	Sheet 1 of 1		

