


Lab Notebook Entry from LeCroy DSO  
DSO S/N: LCRY0614N49164  
User: LeCroyUser  
Time: 1/1/2002 12:23:55 AM

1/1/2002 12:23:55 AM

RxClk vs LOCK  
Clk Only  
Text with Background



#### Channel Status

	C1	C2	C3
<b>Vertical</b>			
V / Div	100 mV	100 mV	1.00 V
Offset	-1.3000 V	-1.3000 V	440 mV
Coupling	DC1MΩ	DC1MΩ	DC1MΩ
BW-Limit	Full	Full	Full
Probe	10	10	10
Sweeps	1 #	1 #	1 #

#### Acquisition Status

<b>Horizontal</b>	Time / Div	20.0 ns	Sampling Rate	5.0 GS/s
	Time / Pt	200 ps	Sampling Mode	RealTime
	Pts / Div	100.0 S	Trigger Delay	0.0 ns
<b>Trigger</b>	Mode	Stop	Slope	Positive
	Type	Edge	Level	1.288 V
	Source	C2	Coupling	DC

