


Lab Notebook Entry from LeCroy DSO  
DSO S/N: LCRY0614N49164  
User: LeCroyUser  
Time: 1/1/2002 12:16:37 AM

1/1/2002 12:16:37 AM

RxCik vs TxClk  
Clk Only  
Text with background



#### Channel Status

	C1	C2	C3	C4
Vertical	V / Div	100 mV	100 mV	100 mV
	Offset	-1.1500 V	-1.1500 V	-1.4500 V
	Coupling	DC1MΩ	DC1MΩ	DC1MΩ
	BW-Limit	Full	Full	Full
	Probe	10	10	10
	Sweeps	1 #	1 #	1 #

#### Acquisition Status

Horizontal	Time / Div	20.0 ns	Sampling Rate	5.0 GS/s
	Time / Pt	200 ps	Sampling Mode	RealTime
	Pts / Div	100.0 S	Trigger Delay	0.0 ns
Trigger	Mode	Stop	Slope	Positive
	Type	Edge	Level	1.219 V
	Source	C3	Coupling	DC

