







REV.	DESCRIPTION	DRAWN	ECN	DATE
I	sample release (3102-0080)	ERIC	S05-041	06-21'2005
A	NEW RELEASE (3007-0191)	TINA	05-402	12-30'2005
B	SEE ECN	TINA	08-267	10-16'2008

ELECTRICAL PERFORMANCE :

- 1.Impedance : 50 ohms
- 2.Frequency Range : 0~6.0 GHz
- 3.Working Voltage : 170Vrms Maximum
- 4.Dielectric Withstanding Voltage : 500Vrms Minimum



INSULATOR	TEFLON	NONE
CONTACT	Be. COPPER	GOLD 30u"
INSULATOR	TEFLON	NONE
BODY	BRASS	GOLD
DESCRIPTION	MATERIALS	FINISHED

RoHS
COMPLIANT
2002/95/EC

UNLESS OTHERWISE SPECIFIED ALL TOLERANCES ARE :

DIMENSION	ANGLE
INTEGRAL DIMENSIONS ±1.0	ANGULAR DIMENSIONS ±5.0°
1 PLACE DECIMAL ±0.5	HOLES UNDER Ø0.5 ±0.1
2 PLACE DECIMALS ±0.25	ROUGHNESS

	FINISH: SEE TABLE	MATERIAL: SEE TABLE
--	-------------------	---------------------

nicon Precise Corp.

DRAWN BY:	ERIC	DATE:	06-21'2005
ENGR BY:	ERIC	DATE:	06-21'2005
APVD BY:	AS	DATE:	10/17'08

TITLE: MMCX R/A JACK PCB RECEPTACLE

Model NO: 33102

Drawing NO: 12-33102

UNIT:	MM	SIZE:	A4	REV.	B	CAD FILE:
SCALE:	10:1	SHEET	1	OF	1	Z:\NEW DWG\33XXX\33102