




Ethernet : RGMII to Copper



STRAP OPTIONS

PHY Address : 0000

```
RX_D0 = MODE0
```

```

RX_D0  = MODE0
RX_D1  = MODE0

```



Auto-negotiation, 1000/100/10 advertised, Auto MDI-X

LED [2:0] = 000 [Mode 0]

Functional mode: RGMII to Copper

RX_D2, RX_D3 & JTAG_TDO (2:0) = 000

Ethernet : RGMII to SGMII



STRAP OPTIONS

PHY Address : 0001

RX_D0 = MODE1

RX_D1 = MODE0

Auto-negotiation, 1000/100/10 advertised, Auto MDI-X

LED [2:0] = 000 [Mode 0]

Functional mode: SGMII to RGMII

RX_D2, RX_D3 & JTAG_TDO (2:0) = 011