







Rear Type C Gen2 Redriver 1142




File		
<Title>		
Size	Document Number	Rev
D	<Doc>	B00
Date:	Wednesday, July 03, 2024	Sheet 34 of 143




TPS25810 Type C Port	GC1	GC2	TPS25810 Response						
			OUT	WCNN On CC1 or CC2	/POL	/UPP	/AUDIO	/DEBUG	
Nothing Attached	OPEN	OPEN	OPEN	NO	Hi-Z	Hi-Z	Hi-Z	Hi-Z	
UFP Connected	Rd	OPEN	IN1	NO	Hi-Z	LOW	Hi-Z	Hi-Z	
UFP Connected	OPEN	Rd	IN1	NO	LOW	LOW	Hi-Z	Hi-Z	
Powered Cable/No UFP Connected	OPEN	Rd	OP2	NO	Hi-Z	Hi-Z	Hi-Z	Hi-Z	
Powered Cable/No UFP Connected	Rd	OPEN	OPEN	NO	Hi-Z	Hi-Z	Hi-Z	Hi-Z	
Powered Cable/UFP Connected	Rd	Rd	IN1	CC2	Hi-Z	LOW	Hi-Z	Hi-Z	
Powered Cable/UFP Connected	Rd	Rd	IN1	CC1	LOW	LOW	Hi-Z	Hi-Z	
Debug Accessory Connected	Rd	Rd	OPEN	NO	Hi-Z	Hi-Z	Hi-Z	LOW	
Debug Accessory Connected	Rd	OPEN	OP2	NO	Hi-Z	Hi-Z	Hi-Z	Hi-Z	


Rear Type C Gen2 Redriver 1142




File		
<Title>		
Size D	Document Number <Doc>	Rev B00
Date: Wednesday, July 03, 2024 Sheet 36 of 143		

[illegible]

Rear Type C Gen2 Redriver 1142



File <File>		
Size D	Document Number <Doc>	Rev B00
Date: Wednesday, July 03, 2024 Sheet 38 of 143		



CHG	CHG_HI	CC Capability Broadcast	Current Limit	Load Detect Threshold
0	0	STD	1.67 A	NA
0	1	STD	1.67 A	NA
1	0	1.5 A	1.67 A	NA
1	1	3.0 A	3.34 A	1.77 A

TPS25810 Type C Port	CC1	CC2	TPS25810 Response					
			OUT	VCONN On CC1 or CC2	/POL	/UFP	/AUDIO	/DEBUG
Nothing Attached	OPEN	OPEN	OPEN	NO	Hi-Z	Hi-Z	Hi-Z	Hi-Z
UFP Connected	Rd	OPEN	IN1	NO	Hi-Z	LOW	Hi-Z	Hi-Z
UFP Connected	OPEN	Rd	IN1	NO	LOW	LOW	Hi-Z	Hi-Z
Powered Cable/No UFP Connected	OPEN	Rd	OPEN	NO	Hi-Z	Hi-Z	Hi-Z	Hi-Z
Powered Cable/No UFP Connected	Ra	OPEN	OPEN	NO	Hi-Z	Hi-Z	Hi-Z	Hi-Z
Powered Cable/UFP Connected	Rd	Ra	IN1	CC2	Hi-Z	LOW	Hi-Z	Hi-Z
Powered Cable/UFP Connected	Ra	Rd	IN1	CC1	LOW	LOW	Hi-Z	Hi-Z
Debug Accessory Connected	Rd	Rd	OPEN	NO	Hi-Z	Hi-Z	Hi-Z	LOW
Audio Adapter Accessory Connected	Ra	Ra	OPEN	NO	Hi-Z	Hi-Z	LOW	Hi-Z