



NO.	V _{IDX} VOLTAGE RANGE			V _{IDX} TARGET VOLTAGE	SUGGESTED STRAP RESISTORS (1% TOL)		ASSIGNED I2C ADDRESS	
	V _{MIN}	V _{TYP}	V _{MAX}	V _(VDD18) = 1.8 V	R ₁ (kΩ)	R ₂ (kΩ)	7-BIT	8-BIT
0	0	0	0.135 × V _(VDD18)	0	OPEN	10.0	0x0C	0x18
1	0.176 × V _(VDD18)	0.213 × V _(VDD18)	0.247 × V _(VDD18)	0.384	73.2	20.0	0x0E	0x1C
2	0.289 × V _(VDD18)	0.327 × V _(VDD18)	0.363 × V _(VDD18)	0.589	60.4	30.1	0x10	0x20
3	0.407 × V _(VDD18)	0.441 × V _(VDD18)	0.467 × V _(VDD18)	0.793	51.1	40.2	0x12	0x24
4	0.526 × V _(VDD18)	0.555 × V _(VDD18)	0.584 × V _(VDD18)	0.999	40.2	51.1	0x14	0x28
5	0.640 × V _(VDD18)	0.671 × V _(VDD18)	0.701 × V _(VDD18)	1.208	30.1	61.9	0x16	0x2C
6	0.757 × V _(VDD18)	0.787 × V _(VDD18)	0.814 × V _(VDD18)	1.417	18.7	71.5	0x18	0x30
7	0.877 × V _(VDD18)	V _(VDD18)	V _(VDD18)	1.8	10	OPEN	0x1A	0x34