




DSP - I/O




DSP - DEBUG





32MByte SERIAL FLASH





PL4 - POWER AMP SIGNAL OUT1 PLUS POWER MONITOR



SUPPLY MONITORS

I2C BASE ADDRESS IS 90HEX
MEASURES INTERNAL TEMPERATURE TOO.
MAX VIN IS VCC+0V3

