

LEVEL	SETTING
L0	1 kΩ to GND
L1	13 kΩ to GND
L2	F (Float)
L3	59 kΩ to GND

PIN NAME	DESCRIPTION
EN_SMB	Four-level control input used to select SMBus/I2C or Pin control. L0: Pin mode L1: RESERVED L2: RESERVED L3: I2C or SMBus Slave Mode
EQQ_ADDR0	The 4-Level Control Input pins of SN75LVPE4410 is defined according to Table 4. In I2C or SMBus Mode (EN_SMB =L3), the pins are used to set the I2C or SMBus address of the device. The pin state is read on power up and decoded according to Table 5.
EQQ_ADDR1	In Pin mode (EN_SMB = L0), the pins are decoded at power up to control the CTLE boost setting according to Table 1.
GAIN	Sets DC gain of CTLE at power up. L0: Reserved L1: Reserved L2: 0 dB (recommended) L3: 3.5 dB
RX_DET	The RX_DET pin controls the receiver detect function. Depending on the input level, a 50 Ω or >50 kΩ termination to the power rail is enabled. See Table 3 for details.
VOD	Sets TX VOD setting at power up. L0: -6 dB L1: -3.5 dB L2: 0 dB (recommended) L3: -1.5 dB

