


Texas Instruments, Inc. High Speed Interface Products

ONET8551T APD Bonding

Alex Davidson

ONET8551T

11.3Gb/s High Gain Limiting TIA with RSSI



Applications

- 10 Gigabit Ethernet Optical Receivers
- 8x and 10x Fibre Channel Optical Receivers
- SONET OC-192 Optical Receivers
- 10G PON
- 6G & 10G CPRI and OBSAI
- PIN and APD Preamplifiers

Features

- 9GHz Bandwidth
- 10k Ω Differential Transimpedance
- 0.9 μ A_{RMS} Input Referred noise
- -20dBm Sensitivity
- 2.5mA_{pp} Input Overload Current
- Received Signal Strength Indicator
- 92mW Typical Power Dissipation
- Single +3.3V Supply
- -40°C to 100°C Ambient Operation
- On Chip Supply Filter Capacitor
- Die size: 870 μ m x 1036 μ m

Benefits

- One TIA for PIN and APD applications
- High Gain for reduced crosstalk
- Low Bandwidth and Transimpedance Variation over Temperature
- Low Power
- Bandwidth adjustment

ONET8551T


APD Bonding Recommendations

NOTE: MAKE ALL WIREBOND LENGTHS AS SHORT AS POSSIBLE USE A LOW LOOP HEIGHT.

Except wirebond from IN to PD: 0.3nH (300um) was used in simulations


Have 2 versions:

1. Ground both pads 17 and 20.
2. Ground only pad 17.



ONET8551T

APD Bonding Example



Use a header with 50Ω pins