



HDMI-INPUT INTERFACE



PIN STRAPPING SETTINGS	
PIN NAME	Description
I2C_EN/PIN	I2C_EN/PIN = Low; puts device into pin strap mode
PRE_SEL	PRE_SEL = L: -2 dB PRE_SEL = No Connect: 0 dB PRE_SEL = H: Reserved
EQ_SEL/A0	EQ_SEL = L: Fixed EQ at 1.5 dB at 3 GHz EQ_SEL = No Connect: Adaptive EQ EQ_SEL = H: Fixed at 14 dB at 3 GHz
TX_TERM_CTL	TX_TERM_CTL = H, no transmit termination TX_TERM_CTL = L, 75 to 150 Ω termination TX_TERM_CTL = No Connect
SIG_EN	SIG_EN = L: Signal detect circuit disabled; SIG_EN = H: Signal detect circuit enabled;

PIN STRAPING



HDMI-IN CONNECTOR

