


RxCikIn



## Channel Status

	C1	C2
<b>Vertical</b>		
V / Div	100 mV	100 mV
Offset	-1.3000 V	-1.3000 V
Coupling	DC1MΩ	DC1MΩ
BW-Limit	Full	Full
Probe	10	10
Sweeps	1 #	1 #

## Acquisition Status

<b>Horizontal</b>	Time / Div	10.0 ns	Sampling Rate	5.0 GS/s
	Time / Pt	200 ps	Sampling Mode	RealTime
	Pts / Div	50.0 S	Trigger Delay	-6.4000 μs
	Mode	Stop	Slope	Positive
<b>Trigger</b>	Type	Edge	Level	1.296 V
	Source	C2	Coupling	DC

