


TxCikOut



Channel Status

	C1	C2
Vertical		
V / Div	200 mV	200 mV
Offset	-764.0 mV	-774.0 mV
Coupling	DC1MΩ	DC1MΩ
BW-Limit	Full	Full
Probe	10	10
Sweeps	1 #	1 #

Acquisition Status

Horizontal	Time / Div	100 μs	Sampling Rate	500 MS/s
	Time / Pt	2.000 ns	Sampling Mode	RealTime
	Pts / Div	50.0000 kS	Trigger Delay	-426 μs
	Mode	Stop	Slope	Positive
Trigger	Type	Edge	Level	800 mV
	Source	C2	Coupling	DC

