


Lab Notebook Entry from LeCroy DSO  
DSO S/N: LCRY0614N49164  
User: LeCroyUser  
Time: 12/10/2014 3:40:14 PM

12/10/2014 3:40:14 PM

RxCikIn vs DOUT



#### Channel Status

	C1	C2	C3	C4
V / Div	100 mV	100 mV	100 mV	100 mV
Offset	-1.3000 V	-1.3000 V	0.0 mV	0.0 mV
Coupling	DC1MΩ	DC1MΩ	DC1MΩ	DC1MΩ
BW-Limit	Full	Full	Full	Full
Probe	10	10	10	10
Sweeps	1 #	1 #	1 #	1 #

#### Acquisition Status

	Time / Div	10.0 ns	Sampling Rate	5.0 GS/s
Horizontal	Time / Pt	200 ps	Sampling Mode	RealTime
	Pts / Div	50.0 S	Trigger Delay	-6.4000 μs
	Mode	Stop	Slope	Positive
Trigger	Type	Edge	Level	1.296 V
	Source	C2	Coupling	DC

