





EN SMB

Select the electrical voltage of SMBus interface. 2.5-V/3.3-V or 1.8-V:
 1: 1 k to VDD - 1.8-V SMBus interface
 F: Float - 1.8-V SMBus interface
 0: 1 k to GND - 2.5-V/3.3-V SMBus interface

READ_EN_N This pin must be pulled high or left floating for normal operation in SMBus Slave Mode.
 READ_EN_N This pin can be held low for normal floating operation in SMBus Master Mode.

If SMBus Slave Mode will be used for all device configurations, an EEPROM is not needed.



- 0: 1 k to GND
- R: 10 k to GND (20 k Ω also acceptable)
- F: Float
- 1: 1 k to VDD




Table 7. SMBus Address Map

8-BIT WRITE ADDRESS [HEX]	REQUIRED ADDRESS PIN STRAP VALUE	
	ADDR1	ADDR0
0x30	0	0
0x32	0	R
0x34	0	F
0x35	0	1
0x38	R	0
0x3A	R	R
0x3C	R	F
0x3E	R	1
0x40	F	0
0x42	F	R
0x44	F	F
0x46	F	1
0x48	1	0
0x4A	1	R
0x4C	1	F
0x4E	1	1

Delta Network Infrastructure (DNI)

12_Re-limer

Rev	Document Number	Rev
C	1AD00-K0000X	XX
Issue	Friday, October 08, 2009	Page 12 of 32