

PCA9617 Side A PU2.2K, Side B PU 4.7K			
Side	device/address/return value	Pic	Note
3V3	0x68 0x00=0x06		PCA9617 Side B VOL 520mV SI5395D VOL 80mV
1V8	0x68 0x00=0x06		PCA9617 Side A VOL 40mV

TCA9803 Side A PU2.2K, Side B NO PU			
Side	device/address/return value	Pic	Note
3V3	0x68 0x00=0x06		TCA9803 Side B VOL 220mV SI5395D VOL 80mV
1V8	0x68 0x00=0x06		TCA9803 Side A VOL 40mV

PCA9617 Side A PU2.2K, Side B PU 4.7K																																	
Side	device/address/return value	Pic	Note																														
1V8	read 0x59 0x00=0x00	<table border="1"> <thead> <tr> <th>Signal</th> <th>Value</th> <th>Mean</th> <th>Min</th> <th>Max</th> <th>Std Dev</th> </tr> </thead> <tbody> <tr> <td>High</td> <td>1.60 V</td> <td>2.40</td> <td>1.64</td> <td>2.40</td> <td>725m</td> </tr> <tr> <td>Low</td> <td>0.00 V</td> <td>697m</td> <td>0.00</td> <td>1.20</td> <td>859m</td> </tr> <tr> <td>High</td> <td>1.88 V</td> <td>2.65</td> <td>1.20m</td> <td>2.48</td> <td>863m</td> </tr> <tr> <td>Low</td> <td>85.0mV</td> <td>1.10</td> <td>-88.9m</td> <td>1.24</td> <td>1.35</td> </tr> </tbody> </table>	Signal	Value	Mean	Min	Max	Std Dev	High	1.60 V	2.40	1.64	2.40	725m	Low	0.00 V	697m	0.00	1.20	859m	High	1.88 V	2.65	1.20m	2.48	863m	Low	85.0mV	1.10	-88.9m	1.24	1.35	
Signal	Value	Mean	Min	Max	Std Dev																												
High	1.60 V	2.40	1.64	2.40	725m																												
Low	0.00 V	697m	0.00	1.20	859m																												
High	1.88 V	2.65	1.20m	2.48	863m																												
Low	85.0mV	1.10	-88.9m	1.24	1.35																												
3V3	read 0x59 0x00=0x00	<table border="1"> <thead> <tr> <th>Signal</th> <th>Value</th> <th>Mean</th> <th>Min</th> <th>Max</th> <th>Std Dev</th> </tr> </thead> <tbody> <tr> <td>High</td> <td>3.25 V</td> <td>2.55</td> <td>1.54</td> <td>2.40</td> <td>748m</td> </tr> <tr> <td>Low</td> <td>0.00 V</td> <td>576m</td> <td>0.00</td> <td>1.20</td> <td>1.03</td> </tr> <tr> <td>High</td> <td>3.26 V</td> <td>2.81</td> <td>1.00m</td> <td>2.48</td> <td>833m</td> </tr> <tr> <td>Low</td> <td>56.0mV</td> <td>1.52</td> <td>-88.0m</td> <td>1.24</td> <td>1.48</td> </tr> </tbody> </table>	Signal	Value	Mean	Min	Max	Std Dev	High	3.25 V	2.55	1.54	2.40	748m	Low	0.00 V	576m	0.00	1.20	1.03	High	3.26 V	2.81	1.00m	2.48	833m	Low	56.0mV	1.52	-88.0m	1.24	1.48	
Signal	Value	Mean	Min	Max	Std Dev																												
High	3.25 V	2.55	1.54	2.40	748m																												
Low	0.00 V	576m	0.00	1.20	1.03																												
High	3.26 V	2.81	1.00m	2.48	833m																												
Low	56.0mV	1.52	-88.0m	1.24	1.48																												

TCA9803 Side A PU2.2K, Side B NO PU																																	
Side	device/address/return value	Pic	Note																														
1V8	read 0x59 0x00	<table border="1"> <thead> <tr> <th>Signal</th> <th>Value</th> <th>Mean</th> <th>Min</th> <th>Max</th> <th>Std Dev</th> </tr> </thead> <tbody> <tr> <td>High</td> <td>1.38 V</td> <td>1.80</td> <td>1.80</td> <td>1.80</td> <td>0.00</td> </tr> <tr> <td>Low</td> <td>0.00 V</td> <td>0.00</td> <td>0.00</td> <td>0.00</td> <td>0.00</td> </tr> <tr> <td>High</td> <td>1.38 V</td> <td>1.80</td> <td>1.80</td> <td>1.80</td> <td>0.00</td> </tr> <tr> <td>Low</td> <td>0.00 mV</td> <td>0.00</td> <td>0.00</td> <td>0.00</td> <td>0.00</td> </tr> </tbody> </table>	Signal	Value	Mean	Min	Max	Std Dev	High	1.38 V	1.80	1.80	1.80	0.00	Low	0.00 V	0.00	0.00	0.00	0.00	High	1.38 V	1.80	1.80	1.80	0.00	Low	0.00 mV	0.00	0.00	0.00	0.00	read 0x70 channel 2 0x59 makes I2C bus crash
Signal	Value	Mean	Min	Max	Std Dev																												
High	1.38 V	1.80	1.80	1.80	0.00																												
Low	0.00 V	0.00	0.00	0.00	0.00																												
High	1.38 V	1.80	1.80	1.80	0.00																												
Low	0.00 mV	0.00	0.00	0.00	0.00																												
3V3	read 0x59 0x00	<table border="1"> <thead> <tr> <th>Signal</th> <th>Value</th> <th>Mean</th> <th>Min</th> <th>Max</th> <th>Std Dev</th> </tr> </thead> <tbody> <tr> <td>High</td> <td>3.32 V</td> <td>3.32</td> <td>3.32</td> <td>3.32</td> <td>0.00</td> </tr> <tr> <td>Low</td> <td>200mV</td> <td>200m</td> <td>200m</td> <td>200m</td> <td>0.00</td> </tr> <tr> <td>High</td> <td>3.32 V</td> <td>3.32</td> <td>3.32</td> <td>3.32</td> <td>0.00</td> </tr> <tr> <td>Low</td> <td>400mV</td> <td>400m</td> <td>400m</td> <td>400m</td> <td>0.00</td> </tr> </tbody> </table>	Signal	Value	Mean	Min	Max	Std Dev	High	3.32 V	3.32	3.32	3.32	0.00	Low	200mV	200m	200m	200m	0.00	High	3.32 V	3.32	3.32	3.32	0.00	Low	400mV	400m	400m	400m	0.00	read 0x70 channel 2 0x59 makes I2C bus crash
Signal	Value	Mean	Min	Max	Std Dev																												
High	3.32 V	3.32	3.32	3.32	0.00																												
Low	200mV	200m	200m	200m	0.00																												
High	3.32 V	3.32	3.32	3.32	0.00																												
Low	400mV	400m	400m	400m	0.00																												

see I2C_tree.png

