

## 4 to 20mA Analog Output Signal Driving

Power requirement  
 10V\*25mA, 250mW;  
 12V\*25mA, 300mW;  
 24V\*25mA, 600mW;

Voltage drop on 250R  
 20mA\*250R=5.00V, 0.10W  
 25mA\*250R=6.25V, 0.16W

External  
 Rload: <=250Ohm

