

	MAX478CSA+	LT2178CS8#PBF	OPA2197 IDR	OPA2196IDR	LMC6062AIMX/NOPB	OPA2187IDR	OPA2191
Operating Temp (°C)	0°C to +70°C	0°C to 70°C	-40 to +125°C	-40 to +125°C	-40 to +85°C	-40 to +125°C	-40 to +125°C
GBP(MHz)	0.085	0.085	10	2.5	0.1	0.55	2.5
SR - Slew Rate (V/us)	0.04	0.04	20	5.5	0.035	0.2	5.5
CMRR	106	106	140	140	85	130	120
Input bias current(nA)	6	6	0.02	0.02	0.0001	0.35	0.02
Input offset voltage (mV)	0.48	0.4	0.1	0.1	0.35	0.01	0.025
PSRR	112	112	130	130	75	160	120
Input Noise Voltage Density(nV/√Hz)	49	49	12.5	24	83	20	15
Operating Current per Channel IS (uA)	25	25	1500	200	16	150	200
Voltage gain(dB)	116.9	116.9	134	120	132	140	134
Input offset current (nA)	0.35	0.35	0.02	0.02	0.001	0.5	0.02
Package	SOIC 8	SOIC 8	SOIC 8	SOIC 8	SOIC 8	SOIC-8	SOIC 8