




SYS BLOCK



SonoDAQ-POE



POWER BLOCK





Title BLOCK		
Size A3	Document Number SonoDAQ-POE	Rev V03
Date: Friday, July 11, 2025	Sheet 2	of 8


INTERFACE

ENET+USB+CTRL


USB PD



Adapter PWR




CAN TO DB9




POE PWR IN/OUT

排针





Manufacture Hole



Title			INTERFACE		
Size	Document Number		CustomSondAQ-POE		Rev
Date:	Friday, July 11, 2025	Sheet	3	of	8




ENETO 1000M -PSE_RJ45

Transformer



- 3 ENETO_PSE_TRX1AK ENETO_PSE_TRX1AP
- 3 ENETO_PSE_TRX1AK ENETO_PSE_TRX1AN
- 3 ENETO_PSE_TRX1BK ENETO_PSE_TRX1BP
- 3 ENETO_PSE_TRX1BK ENETO_PSE_TRX1BN
- 3 ENETO_PSE_TRX1CK ENETO_PSE_TRX1CP
- 3 ENETO_PSE_TRX1CK ENETO_PSE_TRX1CN
- 3 ENETO_PSE_TRX1DK ENETO_PSE_TRX1DP
- 3 ENETO_PSE_TRX1DK ENETO_PSE_TRX1DN
- 3 ENETO_PSE_ACT_LED ENETO_PSE_ACT_LED
- 3 ENETO_PSE_LINK_LED ENETO_PSE_LINK_LED



PSE_RJ45



Title		
ENETO_1000M-PSE_RJ45		
Size	Document Number	Rev
A3	SonoDAQ-POE	V03
Date:	Friday, July 11, 2025	Sheet 4 of 8




ENET0 1000M -PD_RJ45

Transformer





- 3 ENET0_PD_TRX2AP <-> ENET0_PD_TRX2AP
- 3 ENET0_PD_TRX2AN <-> ENET0_PD_TRX2AN
- 3 ENET0_PD_TRX2BP <-> ENET0_PD_TRX2BP
- 3 ENET0_PD_TRX2BN <-> ENET0_PD_TRX2BN
- 3 ENET0_PD_TRX2CP <-> ENET0_PD_TRX2CP
- 3 ENET0_PD_TRX2CN <-> ENET0_PD_TRX2CN
- 3 ENET0_PD_TRX2DP <-> ENET0_PD_TRX2DP
- 3 ENET0_PD_TRX2DN <-> ENET0_PD_TRX2DN
- 3 ENET0_PD_ACT_LED <-> ENET0_PD_ACT_LED
- 3 ENET0_PD_LINK_LED <-> ENET0_PD_LINK_LED

PD_RJ45






Title		
ENET0_1000M-PD_RJ45		
Size	Document Number	Rev
A3	SonoDAQ-POE	V03
Date:	Friday, July 11, 2025	Sheet 5 of 8

USB3 0-TO-ENET1



USB3.0 I/F



Title		TYPE_C-USB3_0
Size	Document Number	SonoDAQ-POE
A3	Date:	Friday, July 11, 2025
Sheet		6 of 8
Rev		v03

