

Stress	Reference	Min Lot Qty	Sample Size / Lot	Condition	Duration	Result
TC	JESD22-A104	3	25	Temperature Cycle -65/150C	500 Cycles	PASS
AC/UHAST	JESD22-A102/JESD22-A118	3	25	Autoclave 121C or Unbiased HAST 130C / 85% RH	96 Hours	PASS
HTSL	JESD22-A103	3	25	High Temp Storage Bake 150C	1000 Hours	PASS
THB/HAST	JESD22-A101/JESD22-A110	3	25	THB 85C/85%RH or HAST 130C/110C /85%RH	1000 Hours or 96 Hours	PASS
CDM	JESD22-C101	1	3	ESD - CDM	Classification	See datasheet
HBM	JS-001	1	3	ESD - HBM	Classification	See datasheet
HTOL	JESD22-A108	3	77	Life Test, 125C	1000 Hours	PASS
LU	JESD78	1	3	Latch-up	Per JESD78	PASS
MSL	JEDEC J-STD-020E			Per JEDEC J-STD-020E	Classification	See datasheet