







ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: SLHR017	REV: B	SUN REV: Not In VersionControl
LAYER NAME = Top Overlay	TID #: N/A		
PLOT NAME = Top Overlay	GENERATED : 5/22/2020 12:22:28 PM	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: SLHR017	REV: B	SUN REV: Not In VersionControl
LAYER NAME = Top Solder	TID #: N/A		
PLOT NAME = Top Solder Mask	GENERATED : 5/22/2020 12:22:31 PM	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: SLHR017	REV: B	SUN REV: Not In VersionControl
LAYER NAME = Top Layer	TID #: N/A		
PLOT NAME = Top Layer	GENERATED : 5/22/2020 12:22:33 PM	TEXAS INSTRUMENTS	



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: SLHR017	REV: B	SUN REV: Not In VersionControl
LAYER NAME = Bottom Layer	TID #: N/A		
PLOT NAME = Bottom Layer	GENERATED : 5/22/2020 12:22:34 PM	TEXAS INSTRUMENTS	





ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: SLHR017	REV: B	SUN REV: Not In VersionControl
LAYER NAME = Bottom Solder	TID #: N/A		
PLOT NAME = Bottom Solder Mask	GENERATED : 5/22/2020 12:22:36 PM	TEXAS INSTRUMENTS	



DRILL TABLE:

Symbol	Count	Hole Size	Plated	Hole Type	Tolerance(Mils)	Tenting
A	109	12.00mil (0.305mm)	PTH	Round	+0/-12	Both
O	8	35.43mil (0.900mm)	PTH	Round		
X	6	20.00mil (0.508mm)	PTH	Round		
D	4	125.98mil (3.200mm)	PTH	Round	+/-3	
E	3	214.57mil (5.450mm)	PTH	Round	+/-3	
□	2	40.00mil (1.016mm)	PTH	Round		
☆	2	51.18mil (1.300mm)	PTH	Round		
134 Total						

ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: SLHR017	REV: B	SUN REV: Not In VersionControl
LAYER NAME = Drill Drawing	TID #: N/A		
PLOT NAME = Drill Drawing	GENERATED : 5/22/2020 12:22:38 PM	TEXAS INSTRUMENTS	



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: SLHR017	REV: B	SUN REV: Not In VersionControl
LAYER NAME = M2 Board Dimensions	TID #: N/A		
PLOT NAME = Board Dimensions	GENERATED : 5/22/2020 12:22:41 PM	TEXAS INSTRUMENTS	