


File	<Title>	Rev	<Rev Code>
Size	Document Number		
C	<Doc>		
Date:	Tuesday, December 13, 2022	Sheet	1 of 1




WRT_PORT_A >>> WRTA
 WRT_PORT_B >>> WRTB

CLK_PORT_A >>> CLKA
 CLK_PORT_B >>> CLKB


SLEEP_DAC >>> SLEEP
 MODE_DAC >>> MODE
 SLEEP HIGH: DAC IN POWER-DOWN MODE
 SLEEP LOW: DAC IN OPERATING MODE
 MODE HIGH: DUAL BUS
 MODE LOW: INTERLEAVED MODE

File	<Title>	Rev	<Rev Code>
Size	Document Number		
C	<Doc>		
Date:	Tuesday, December 13, 2022	Sheet	1 of 1



AC coupling : Omitout 49.9k resistor and REF 1.2V

Opamp Gain = 60B For LFF
 Gain = 120B For BFF



AC coupling : Omitout 49.9k resistor and REF 1.2V

Opamp Gain = 60B For LFF
 Gain = 120B For BFF

BFF = AC Coupling
 LFF = DC Coupling

