

# Titanis 2.4 GHz Swivel SMA Antenna

Part No. 2010B4844-01 / 2010B6090-01

**Product Specification** 

#### 1 Features

- Designed for 2.4 GHz applications: Bluetooth<sup>®</sup>, Wi-Fi<sup>®</sup> (802.11b/g), ZigBee<sup>®</sup>, etc.
- Antenna with a SMA male connector
- Also available as SMA reverse thread to meet FCC regulations, part 15
- High efficiency
- Supplied in bulk

### 2 Description

Titanis is intended for use with all 2.4 GHz applications. The antenna is fitted with a SMA male connector and a blade made of flexible material that can be rotated 360 degree.

No external matching network required.

### 3 Applications

- Development tools
- Test equipment
- Access points, routers, etc
- Printers



Integrated Antenna Solutions

#### 4 Part number

Titanis Standard SMA - male: 2010B4844-01

Titanis Reverse thread SMA - male: 2010B6090-01

#### 5 General data


Product name	Titanis 2.4 GHz
Part Number	2010B4844-01 (Standard SMA – male)
	2010B6090-01 (Reverse thread SMA – male)
Frequency	2.4 – 2.5 GHz
Polarization	Linear
Operating temperature	-40 °C to +85 °C
Impedance	50 Ω
Weight	7.1 g
Antenna type	Swivel external
Dimensions	20 x 19.5 x 62.5 [mm]

#### 6 Electrical characteristics


	Typical performance	Conditions
Peak gain	2.2 dBi	
Average gain	-1.0 dBi	
Average efficiency	80%	Data given for the 2.4 – 2.5 GHz frequency range
Maximum Return Loss	-13 dB	
Maximum VSWR	1.6:1	

## 7 Electrical performance


#### 7-1 Return Loss



#### **7-2 VSWR**




#### 7-3 **Antenna patterns**



Patterns show combined polarisations

Integrated Antenna Solutions

### 8 Antenna dimensions



 A
 B
 H1
 H2
 H3
 W1
 W2

 Height
 Height
 Height
 Width
 Width

 7 ± 0.2
 12.5 ± 0.5
 62.5 ± 0.5
 48.3 ± 0.5
 9.5 ± 0.5
 20 ± 0.3
 19.5 ± 0.3

Dimensions in mm

## 9 Hazardous material regulation conformance

The antenna has been tested to conform to RoHS requirements. A certificate of conformance is available from Antenova's website.

## 10 Packaging


### 10-1 Optimal storage conditions

Temperature	-10°C to 40°C	
Humidity	Less than 75% RH	
Shelf Life	48 Months	
Storage place	Away from corrosive gas and direct sunlight	

### 10-2 Packaging information

The antennas are delivered in bulk, enclosed in plastic bags.

### 10-3 Bag label information



Dimensions in mm



## www.antenova.com

#### **Corporate Headquarters**

Antenova Ltd. Far Field House Albert Road Stow-cum-Quy Cambridge CB25 9AR

#### **North America Headquarters**

Antenova Ltd. Rogers Business Park 2541 Technology Drive Suite 403 Elgin, IL 60124

#### **Asia Headquarters**

Antenova Asia Ltd. 4F, No. 324, Sec. 1, Nei-Hu Road Nei-Hu District Taipei 11493 Taiwan, ROC

 Tel:
 +44 1223810600
 Tel:
 +1 (847) 551 9710
 Tel:
 +886 (0) 2 8797 8630

 Fax:
 +44 1223 810650
 Fax
 +1 (847) 551 9719
 Fax:
 +886 (0) 2 8797 6890

 Email:
 info@antenova.com
 Email:
 info@antenova.com

**Copyright**® **2007 Antenova Ltd.** All Rights Reserved. Antenova® and RADIONOVA® are trademarks of Antenova Ltd. Any other names and/or trademarks belong to their respective companies.

The materials provided herein are believed to be reliable and correct at the time of print. Antenova does not warrant the accuracy or completeness of the information, text, graphics or other items contained within these information. Antenova further assumes no responsibility for the use of this information, and all such information shall be entirely at the user's risk.

