


CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect




ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	0.035 ohms max.
INDUCTANCE	1-2 10kHz, 100mV, Ls	355.00μH ±20%
SATURATION CURRENT	1-2 30% rolloff from initial	20A
DISTRIBUTED CAPACITANCE	1-2 100mVAC, Cs	10.0pF max.
DIELECTRIC	1-Core 1000VDC, 1 second	1000VDC, 1 minute



Wire size: 4mm width by 0.8mm thickness



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Rated Current: 13 Amps

Preliminary
Confidential

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability. Marking method, font and color may vary on preproduction samples.

DFM		Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.001 [.03]	DRAWING TITLE TRANSFORMER	PART NO. 760801403
DATE		Method: Tray PKG-TBD		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		
ENG	CHC					
REV.	00					
DATE	11/4/2021	www.we-online.com/midcom				SPECIFICATION SHEET 1 OF 1