

CERTIFICATION DATA SHEET

Model#: 48T17D2000 K
CONN. DIAGRAM: A-EE7308
OUTLINE: A-SS75080-575

WINDING#: TE48413 NONE 3
ASSEMBLY: F1 ONLY

TYPICAL MOTOR PERFORMANCE DATA

HP	KW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
1/4&1/4	.187&.187	1800	1725&1425	48	DP	M	B

PH	Hz	VOLTS	FL AMPS	START TYPE	DUTY	INSL	S.F	AMB°C	ELEVATION
3	60/50	208- 230/460#190/ 380	1.2- 1.3/.65&1.4/.7	ACROSS THE LINE	CONTINUOU S	B3	1.35/1.35	40	3300

FULL LOAD EFF: 62&66.5	3/4 LOAD EFF: 56	1/2 LOAD EFF: 47	GTD. EFF	ELEC. TYPE	NO LOAD AMPS
FULL LOAD PF: 58&65	3/4 LOAD PF: 49.5	1/2 LOAD PF: 40.5	57.5	SQ CAGE IND RUN	1.2 / .6

F.L. TORQUE	LOCKED ROTOR AMPS	L.R. TORQUE	B.D. TORQUE	F.L. RISE°C
0.76 LB-FT	6.8 / 3.4	2.8 LB-FT 368	3.4 LB-FT 447	32

SOUND PRESSURE @ 3 FT.	SOUND POWER	ROTOR WK^2	MAX. WK^2	SAFE STALL TIME	STARTS /HOUR	APPROX. MOTOR WGT
60 dBA	70 dBA	0.03 LB-FT^2	0 LB-FT^2	10 SEC.	0	16 LBS.

***** SUPPLEMENTAL INFORMATION *****

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
STANDARD	STANDARD	RIGID	HORIZONTAL	FALSE	NONE	FALSE	NONE	STANDARD

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	OPE						
BALL	BALL						
6203	6203	STANDARD	STANDARD 48	NONE	NONE	STANDARD	ROLLED STEEL

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE /n HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs			
NONE	NOT	NONE	NONE	NONE	FALSE	NONE VOLTS

* N O T E S *	INVERTER TORQUE: NONE
	INV. HP SPEED RANGE: NONE
	ENCODER: NONE
	NONE NONE NONE NONE PPR
	BRAKE: NONE NONE
	NONE P/N NONE
	NONE NONE
	- FT-LB NONE V NONE Hz

DATE: 02/08/2017 07:35:00 PM
 FORM 3531 REV.3 02/07/99
 ** Subject to change without notice.