


REVISIONS

REV.	REV.	DESCRIPTION	DATE	APPROVED



SIZE	QTY	SYM	PLATED	TOL
13	61	+A	YES	+/-0.003
18	354	+B	YES	+/-0.003
20	13	+C	YES	+/-0.003
28	2	+D	YES	+/-0.003
30	188	+E	YES	+/-0.003
31.5	4	+F	YES	+/-0.003
35	4	+G	YES	+/-0.003
38	4	+H	YES	+/-0.003
40	64	+I	YES	+/-0.003
41	12	+J	YES	+/-0.003
42	110	+K	YES	+/-0.003
43	10	+L	YES	+/-0.003
45	2	+M	YES	+/-0.003
52	4	+N	NO	+/-0.003
52	32	+O	YES	+/-0.003
55	23	+P	YES	+/-0.003
60	8	+Q	YES	+/-0.003
63	24	+R	YES	+/-0.003
67	6	+S	YES	+/-0.003
70.87	3	+T	YES	+/-0.003
75	8	+U	YES	+/-0.003
76	8	+V	YES	+/-0.003
92	2	+W	YES	+/-0.003
96	2	+X	NO	+/-0.003
110	4	+Y	YES	+/-0.003
124	2	+Z	YES	+/-0.003
125	8	+AA	YES	+/-0.003
137.8	2	+BB	NO	+/-0.003
141	8	+CC	YES	+/-0.003
180	9	+DD	NO	+/-0.003
250	7	+EE	YES	+/-0.003

1 APPLICATION USED ON	2 CONTRACT NO. Primary Side	3 DWG. NO. www.WSTSCORP.com CHK: 8/13	TEXAS INSTRUMENTS	
NEXT ASSY.	P.E.:	DES ENG.:		
4 UNLESS OTHERWISE SPECIFIED		P.C.:	TITLE: FABRICATION DRAWING,	
5 1. TOLERANCES: LINEAR = : 0.26 (.010) ANGULAR = : 0.50°		O.C.:	C2000 Solar Micro Inverter	
6 2. ALL DIMENSIONS ARE IN MM (INCHES).		C.M.:	ENG'D BY: OTHER: DRAWING NO.: C2000SolarMicroInverter	
7 MATERIAL: SEE NOTE FINISH: SEE NOTE		REL.:	SIZE: B	REV: 4.0
8 DO NOT SCALE DRAWING		MFG.:	CAGE CODE NO.:	
		ENG'D BY:	DRAWING NO.:	
		OTHER:	OTHER:	
		OTHER:	OTHER:	
		SCALE: 1:1	SHEET 1 OF 1	